

Solution details for

2224R024SR + 22/2 308:1

Your comments

Your Requirements

Load transmission	Direct rotational	
Ambient temperature	22	°C
Available diameter	30	mm
Available length	100	mm
Available supply voltage	24	V
Available current	5	A
Efficiency, min.	10	%
Required load speed	10	1/min
Required load torque	0,04	Nm


Results of the Load Calculation

Load current	14,73	mA
Load voltage	9,91	V
Motor winding temperature	23,49	°C
Motor housing temperature	23,45	°C
Required motor torque	0,23	mNm
Required motor speed	3.079,54	1/min
Output power	41,89	mW
Efficiency (over all)	28,7	%


Overall Dimensions

Diameter	23,8	mm
Length	59,4	mm
Mass	128	g

Operating Area



Characteristic curves



Motor Characteristic Data

Nominal voltage	U_N	24	V
Terminal resistance	R	36,3	Ω
Torque constant	k_M	29,1	mNm/A
No load speed	n_0	7.800	1/min
Stall torque	M_H	19	mNm
Speed constant	k_n	328	1/min/V
Rotor inductance	L	0,8	mH
Slope of n-M curve	$\Delta n/\Delta M$	411	1/min/mNm
Rotor inertia	J	2,6	gcm ²
Mechanical time constant	τ	11	ms
Efficiency max.	η_{max}	81	%

Gearhead Characteristic Data

Housing material	metal
Geartrain material	metal
Backlash at no load	3 °
Bearings on output shaft	sintered bearings, ball bearings, preloaded
Shaft load, max. radial	3 N
Shaft load, max. axial	5 N
Shaft press fit force, max.	50 N
Number of gear stages	6
Reduction ratio	308 :1
Calculated reduction	307.95375192901 :1
Continuous torque	100 mNm
Mass	82 g
Efficiency, max.	66 %
Gearshaft diameter	4 mm
Gearhead diameter	23,8 mm

Contact

Do you have any questions regarding FAULHABER Products, our Services, or other Drive System related issues?
Please contact your local representative or fill out our contact form.
<https://www.faulhaber.com/contact/>

General Terms and Conditions of Business and Purchase

Our General Terms and Conditions of Business and Purchase you'll find on <https://www.faulhaber.com/gtc>