

Micro Planetary Gearheads



0,88 mNm

For combination with Brushless DC-Motors

Series 03B

	03B
Housing material	plastic
Geartrain material	steel
Recommended max. input speed for:	
– continuous operation	15 000 min ⁻¹
Backlash, at no-load	≤ 4 °
Bearings on output shaft	sleeve bearing
Shaft load, max.:	
- radial (2 mm from mounting face)	≤ 1 N
– axial	≤ 1 N
Shaft press fit force, max.	≤ 1 N
Shaft play:	
– radial (2 mm from mounting face)	≤ 0,07 mm
– axial	≤ 0,15 mm
Operating temperature range	- 20 + 60 °C

Technical data			
Number of gear stages		2	3
Continuous torque	mNm	0,28	0,88
Intermittent torque	mNm	0,42	1,32
Mass without motor, ca.	g	0,2	0,18
Efficiency, max.	_	-	-
Direction of rotation, drive to output	t	=	=
Reduction ratio		25:1	125:1
(exact)			
L2 [mm] = length without motor		6,0	6,0
L1 [mm] = length with motor 0308	4В	12,6	12,6

Note: These gearheads are available only with motors mounted.

