

**NEW**

# Linear Actuators

**40 N**

**Gearhead with integrated Lead Screw, high load**

For combination with  
DC-Micromotors  
Brushless DC-Motors  
Stepper Motors

## Series 08L ... HL

Values at 22°C

	3	4	5
Number of gear stages	3	4	5
Reduction ratio (exact)	64:1	256:1	1 024:1
Continuous output speed, max. <sup>1)</sup>	mm/s 1,6	0,4	0,1
Peak output speed, max. <sup>1)</sup>	mm/s 2,1	0,5	0,1
Continuous input speed, max.	min <sup>-1</sup> 12 000	12 000	12 000
Peak input speed, max.	min <sup>-1</sup> 16 000	16 000	16 000
Continuous axial force, avg.	N 27	35	40
Peak axial force, dynamic, max.	N 35	40	50
Peak axial force, static, max.	N 80	80	80
Output power, max.	W 0,073	0,021	0,006
Efficiency of gearhead/coupler, max.	% 70	60	55
Efficiency of screw, max.	% 35	35	35
Mass inertia incl. screw, max. <sup>2)</sup>	gmm <sup>2</sup> 0,13	0,129	0,129
Accuracy, screw standard length, max.	µm 100	100	100
Radial load, max. (50 mm from flange)	N 5	5	5
Gearhead backlash, at no-load, typical	° 3	3	3
Radial play (screw, 3,5 mm from flange)	mm ≤ 0,06	≤ 0,06	≤ 0,06
Axial play:			
– screw	mm 0	0	0
– nut	µm 80	80	80
Screw length from flange:			
– standard	mm 50	50	50
– max.	mm 65	65	65
Length without motor L2	mm 15,7	18,4	21,1
Mass <sup>2)</sup>	g 6,8	7,6	8,5
Screw type <sup>3)</sup>	3x0,5 (mm) proprietary thread profile		
Screw material	stainless steel		
Nut material	cylindrical, plastic		
Housing material	stainless steel		
Geartrain material	steel		
Bearings on output shaft	ball bearings, preloaded		
Operating temperature range	°C -30 ... +80		

<sup>1)</sup> According to selected reduction ratio, screw supported

<sup>2)</sup> Standard length and standard nut

<sup>3)</sup> Right handed, screw direction of rotation same as motor shaft.


**Note:**

The display shows the range of possible operation points of the drives at a given ambient temperature of 22°C.


The diagram indicates the recommended output speed in relation to the available output axial force.

For the standard screw both supported and not, the diagram shows also the critical speeds and the buckling forces.

- - - Critical speed <sup>3)</sup> (fixed-free), 179 mm/s
- - - Critical speed <sup>3)</sup> (fixed-single), 950 mm/s
- - - Buckling force <sup>3)</sup> (fixed-free), 195 N
- - - Buckling force <sup>3)</sup> (fixed-single), 1563 N



### Dimensional drawing



### Options

Example product designation: **08L 64:1 KL1 HL 3x0.5 50 KWL1**

Option	Type	Description
KL1	Gearhead ambient conditions	Low temperature range of -55°C to +100°C
KL2	Gearhead ambient conditions	Vacuum down to 10 <sup>-5</sup> Pa @ 22°
KL3	Gearhead ambient conditions	Temperature range of -55°C to +150°C and vacuum down to 10 <sup>-5</sup> Pa @ 60°C
15	Screw	Standard length (lengths from 15 mm to 65 mm are available in 1mm increments)
25	Screw	Standard length (lengths from 15 mm to 65 mm are available in 1mm increments)
50	Screw	Standard length (lengths from 15 mm to 65 mm are available in 1mm increments)
KWS1	Screw	Bearing tip/journal (Ø 2mm, L=2.5mm)
KWL0	Screw ambient conditions	Not lubricated
KWL1	Screw ambient conditions	Low temperature range of -55°C to +100°C
KWL2	Screw ambient conditions	Vacuum down to 10 <sup>-5</sup> Pa @ 22°
KWL3	Screw ambient conditions	Temperature range of -55°C to +150°C and vacuum down to 10 <sup>-5</sup> Pa @ 60°C
KWN1	Nut	Cylindrical bronze nut
KWN3	Nut	Flanged bronze nut
KWN4	Nut	Flanged plastic nut, screw without lubricant
KWN9	Nut	No nut

Note: Specified values may differ from the standard values depending on the option. Please consult your sales representative for further information.

### Product combination

Number of gear stages	3	4	5
L2 [mm] = length without motor	15,7	18,4	21,1
L1 [mm] = length with motor	31,6	34,3	37,0
0816P...SR	39,8	42,5	45,2
AM0820...08	29,5	32,2	34,9