

NEW

Brushless DC-Servomotors
2 Pole Technology

8 mNm
58,5 W

Series 1645 ... BHS

Values at 22°C and nominal voltage	1645 S	024 BHS	036 BHS	048 BHS	
1 Nominal voltage	U_N	24	36	48	V
2 Terminal resistance, phase-phase	R	0,684	1,51	2,81	Ω
3 Efficiency, max.	η_{max}	90	90	90	%
4 No-load speed	n_0	62 000	62 900	61 400	min ⁻¹
5 No-load current, typ. (with shaft \varnothing 3 mm)	I_0	0,0988	0,0674	0,0486	A
6 Stall torque	M_H	137	138	135	mNm
7 Friction torque, static	C_0	0,114	0,114	0,114	mNm
8 Friction torque, dynamic	C_V	$4,49 \cdot 10^{-6}$	$4,49 \cdot 10^{-6}$	$4,49 \cdot 10^{-6}$	mNm/min ⁻¹
9 Speed constant	k_n	2 450	1 650	1 210	min ⁻¹ /V
10 Back-EMF constant	k_E	0,409	0,606	0,825	mV/min ⁻¹
11 Torque constant	k_M	3,9	5,79	7,88	mNm/A
12 Current constant	k_I	0,256	0,173	0,127	A/mNm
13 Slope of n-M curve	$\Delta n / \Delta M$	429	431	432	min ⁻¹ /mNm
14 Terminal inductance, phase-phase	L	46	103	190	μ H
15 Mechanical time constant	τ_m	2,6	2,6	2,7	ms
16 Rotor inertia	J	0,59	0,59	0,59	gcm ²
17 Angular acceleration	α_{max}	2 330	2 350	2 300	$\cdot 10^3$ rad/s ²
18 Thermal resistance	R_{th1} / R_{th2}	3,1 / 22			K/W
19 Thermal time constant	τ_{w1} / τ_{w2}	6,5 / 580			s
20 Operating temperature range:					
– motor		-30 ... +125			°C
– winding, max. permissible		+125			°C
21 Shaft bearings		ball bearings, preloaded			
22 Shaft load max.:					
– with shaft diameter		3			mm
– radial at 40 000 min ⁻¹ (5 mm from mounting flange)		18			N
– axial at 40 000 min ⁻¹ (push only)		9			N
– axial at standstill (push only)		44			N
23 Shaft play:					
– radial	\leq	0,01			mm
– axial	$=$	0			mm
24 Housing material		stainless steel			
25 Mass		58,2			g
26 Direction of rotation		electronically reversible			
27 Speed up to	n_{max}	100 000			min ⁻¹
28 Number of pole pairs		1			
29 Hall sensors		digital			
30 Magnet material		NdFeB			
Rated values for continuous operation					
31 Rated torque	M_N	6,09	6,02	6,1	mNm
32 Rated current (thermal limit)	I_N	1,86	1,24	0,924	A
33 Rated speed	n_N	61 300	62 100	60 600	min ⁻¹


Note: Rated values are calculated with nominal voltage and at a 22°C ambient temperature. The R_{th2} value has been reduced by 25%.


Note:

The diagram indicates the recommended speed in relation to the available torque at the output shaft for a given ambient temperature of 22°C.

The diagram shows the motor in a completely insulated as well as thermally coupled condition (R_{th2} 50% reduced).

The nominal voltage (U_N) curve shows the operating point at nominal voltage in the insulated and thermally coupled condition. Any points of operation above the curve at nominal voltage will require a higher operating voltage. Any points below the nominal voltage curve will require less voltage.



Dimensional drawing

1645 S ... BHS
Option, cable and connection information

 Example product designation: **1645S024BHS**

Option	Type	Description	Connection		
			No.	Function	Colour
			-	Phase C	yellow
			-	Phase B	orange
			-	Phase A	brown
			1	GND	red
			2	U _{DD} (4,5 ... 5,5V)	grey
			3	Hall sensor C	grey
			4	Hall sensor B	grey
			5	Hall sensor A	grey
			6	Reserved	grey
			7	Reserved	grey
			8	Reserved	grey

Standard cable
 Single wires, material PTFE
 AWG24, Phase A/B/C
 Flat cable, material PVC
 AWG28, Pitch 1,27 mm
 Hall A, B, C, U_{DD}, GND

Product combination

Precision Gearheads / Lead Screws	Encoders	Drive Electronics	Cables / Accessories
15/10 17/1 20/1R	IEM3-1024	SC 5004 P SC 5008 S MC 5004 P MC 5005 S	To view our large range of accessory parts, please refer to the "Accessories" chapter.