

Spur Gearheads

Zero Backlash

0,1 Nm

For combination with
DC-Micromotors
Stepper Motors

Series 15/8



	15/8
Housing material	metal
Geartrain material	steel
Recommended max. input speed for:	
– continuous operation	5 000 min ⁻¹
Backlash, at no-load	0 °
Bearings on output shaft	ball bearings, preloaded
Shaft load, max.:	
– radial (6,5 mm from mounting face)	≤ 25 N
– axial	≤ 5 N
Shaft press fit force, max.	≤ 5 N
Shaft play	
– radial (6,5 mm from mounting face)	≤ 0,03 mm
– axial	= 0 mm
Operating temperature range	- 30 ... + 100 °C

Technical data

	4	4	5	5	6	6
Number of gear stages						
Continuous torque	mNm	100	100	100	100	100
Intermittent torque	mNm	300	150	300	150	300
Mass without motor, ca.	g	24	24	26	26	28
Efficiency, max.		-	-	-	-	-
Direction of rotation, drive to output		=	=	≠	≠	=
Reduction ratio ¹⁾ (rounded)		76:1	141:1	262:1	485:1	900:1
						1 670:1
L2 [mm] = length without motor		32,0	32,0	34,1	34,1	36,2
L1 [mm] = length with motor						
	1516E...SR	34,9	34,9	37,0	37,0	39,1
	1524E...SR	42,9	42,9	45,0	45,0	47,1
	AM1524...57	35,5	35,5	37,6	37,6	39,7

¹⁾ The reduction ratios are rounded, the exact values are available on request or at www.faulhaber.com.

Note: These gearheads are available only with motors mounted.



15/8