

Spur Gearheads

Zero Backlash

0,1 Nm

For combination with
DC-Micromotors
Stepper Motors

Series 22/5

	22/5
Housing material	metal
Geartrain material	metal
Recommended max. input speed for:	
– continuous operation	4 000 min ⁻¹
Backlash, at no-load	0 °
Bearings on output shaft	ball bearings, preloaded
Shaft load, max.:	
– radial (6 mm from mounting face)	≤ 100 N
– axial	≤ 5 N
Shaft press fit force, max.	≤ 5 N
Shaft play	
– radial (6 mm from mounting face)	≤ 0,03 mm
– axial	= 0 mm
Operating temperature range	- 30 ... + 100 °C

Technical data

	5	6	7	8	9
Number of gear stages					
Continuous torque	mNm 100	100	100	100	100
Intermittent torque	mNm 400	400	400	400	400
Mass without motor, ca.	g 80	85	90	95	105
Efficiency, max.	-	-	-	-	-
Direction of rotation, drive to output	≠	=	≠	=	≠
Reduction ratio ¹⁾ (rounded)	69,2:1	161:1	377:1	879:1	2 050:1
L2 [mm] = length without motor	50,9	54,6	59,5	63,2	68,1
L1 [mm] = length with motor	2224R...SR 57,8	2230F/R...S 61,6	2232R...SR 66,5	2233F/R...S 70,3	AM2224...14 75,2
	63,6	67,4	72,3	76,1	81,0
	65,8	69,6	74,5	78,3	83,2
	66,2	70,0	74,9	78,7	83,6
	61,4	65,2	70,1	73,9	78,8

¹⁾ The reduction ratios are rounded, the exact values are available on request or at www.faulhaber.com.

Note: These gearheads are available only with motors mounted.

