

## Encoders

magnetic Encoder, digital outputs, 2 channels, 16 - 4096 lines per revolution

For combination with DC-Micromotors

## Series IEH2-4096

	IEH2	-16	-32	-64	-128	-256	-512	-1024	-2048	-4096	
Lines per revolution		16	32	64	128	256	512	1 024	2 048	4 096	
Frequency range, up to <sup>1)</sup> f		5	10	20	40	80	160	320	640	875	kHz
Signal output, square wave		2									Channels
Supply voltage	UDD	4,5	5,5								V
Current consumption, typical <sup>2)</sup>	<b>I</b> DD	typ. 1	5, max. 2	25							mA
Output current, max. <sup>3)</sup>	Ιουτ	2,5									mA
Phase shift, channel A to B <sup>4)</sup>	$\Phi$	90 ± 4	5					90 ± 65	90 ± 75	5	°e
Signal rise/fall time, max. (CLOAD = 50 pF)	tr/tf	0,05 /	0,05								μs
Inertia of sensor magnet	J	0,11									gcm <sup>2</sup>
Operating temperature range		-40	+100								°C

<sup>1)</sup> Velocity (min<sup>-1</sup>) =  $f(Hz) \ge 60/N$ 

<sup>2)</sup>  $U_{DD} = 5$  V: with unloaded outputs

<sup>3)</sup>  $U_{DD}$  = 5 V: low logic level < 0,4 V, high logic level > 4,6 V: CMOS- and TTL compatible

<sup>4)</sup> At 5 000 min<sup>-1</sup>

For combination with Mote	
Dimensional drawing A	<l1 [mm]<="" td=""></l1>
1336 CXR - 123	47,5
Dimensional drawing B	<l1 [mm]<="" td=""></l1>
1516 SR	18,2
1524 SR	26,2
1717 SR	19,4
1724 SR	26,4
2224 SR	26,6
2232 SR	34,6
Dimensional drawing C	<l1 [mm]<="" td=""></l1>
1727 CXR - 123	38,2
1741 CXR - 123	52,2
	5=/=

## Characteristics

These incremental shaft encoders in combination with the FAULHABER DC-Micromotors are used for the indication and control of both shaft velocity and direction of rotation as well as for positioning.

The encoder is integrated in the DC-Micromotors SR-Series and extends the overall length by only 1,4 mm.


A segmented magnetic disc provides a magnetic field which is detected and further processed by an angle sensor. The output signals of both channels consist of a square wave signal with 90° phase shift and up to 4096 impulses per motor revolution.

The encoder is available with different standard resolutions. The supply voltage for the encoder and the DC-Micromotor as well as the two channel output signals are interfaced through a ribbon cable with connector.

Details for the DC-Micromotors and suitable reduction gearheads are on separate catalogue pages.


To view our large range of accessory parts, please refer to the "Accessories" chapter.






option	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	Description	
			No. Function
			1 Motor – *
			2 Motor + *
			3 GND
			4 UDD
			5 Channel B
			6 Channel A
			642
			531
			Cable
			PVC-ribbon cable, 6-conductors, 0,09 mm <sup>2</sup>
			Connector
			EN 60603-13 / DIN-41651, grid 2,54 mm
			* Note:
			DC-Micromotors series CXR have separate motor leads.

## Dimensional drawing A





For notes on technical data and lifetime performance refer to "Technical Information". Edition 2020 Oct. 28



