

Encoders

magnetic Encoder, digital outputs, 3 channels, 256 - 4096 lines per revolution, Line Driver

For combination with DC-Micromotors

Series IEH3-4096L

		IEH3-256L	IEH3-512L	IEH3-1024L	IEH3-2048L	IEH3-4096L	
Lines per revolution	Ν	256	512	1 024	2 048	4 096	
Frequency range, up to ¹⁾	f	80	160	320	640	875	kHz
Signal output, square wave		2+1 Index and	d complement	ary outputs			Channels
Supply voltage	U_{DD}	4,5 5,5					V
Current consumption, typical ²⁾	I DD	typ. 25, max.	43				mA
Index Pulse width ³⁾	P o	90 ± 45		90 ± 65	90 ± 75		°e
Phase shift, channel A to B ³⁾	Φ	90 ± 45		90 ± 65	90 ± 75		°e
Inertia of sensor magnet	J	0,11					gcm ²
Operating temperature range		-40 +100					°C
Accuracy, typ.		0,8					°m
Repeatability, typ.		0,07					°m
Hysteresis		0,35					°m
Edge spacing, min.		225					ns
Mass, typ.		5					g

¹⁾ Velocity (min-1) = $f(Hz) \times 60/N$

Note: The output signals are TIA-422 compatible.

Examples of Line Driver Receivers: ST26C32AB (STM), AM26C32 (TI).

For combination with Motor	r
Dimensional drawing A	<l1 [mm]<="" td=""></l1>
1336 CXR - 123	47,5
Dimensional drawing B	<l1 [mm]<="" td=""></l1>
1516 SR	18,2
1524 SR	26,2
1717 SR	19,4
1724 SR	26,4
2224 SR	26,6
2232 SR	34,6
Dimensional duassina C	.1.4 []
Dimensional drawing C 1727 CXR - 123	< L1 [mm] 38,2
1741 CXR - 123	52,2

Characteristic

These incremental encoders with 3 output channels, in combination with the FAULHABER Motors, are used for the indication and control of both shaft velocity and direction of rotation as well as for positioning.

The encoder is integrated in the DC-Micromotors SR-Series and extends the overall length by only 1,4 mm with 3 output channels and line Driver

A segmented magnetic disc provides a magnetic field which is detected and further processed by an angle sensor. The output signals of both channels consist of a square wave signal with 90° phase shift and up to 4096 impulses and an index impulse per motor revolution.

The Line Driver amplifies the encoder signal which means that long cables can be used without signal degradation.

Differential signal outputs must be decoded by the appropriate receiver module. In addition, a suitable line termination resistance (100 ohm) is possibly useful.

The supply voltage for the encoder and the DC-Micromotor as well as the two channel output signals are interfaced through a ribbon cable with connector.

Details for the DC-Micromotors and suitable reduction gearheads are on separate catalogue pages.

To view our large range of accessory parts, please refer to the "Accessories" chapter.

²⁾ $U_{DD} = 5$ V: with unloaded outputs

³⁾ At 5 000 min-1













