

DC-Micromotors

Graphite Commutation

224 mNm
160 W

Series 3890 ... CR

Values at 22°C and nominal voltage	3890 H	018 CR	024 CR	036 CR	048 CR	
1 Nominal voltage	U_N	18	24	36	48	V
2 Terminal resistance	R	0,21	0,36	0,78	1,38	Ω
3 Efficiency, max.	η_{max}	86	87	87	88	%
4 No-load speed	n_0	5 400	5 400	5 400	5 500	min ⁻¹
5 No-load current, typ. (with shaft \varnothing 6 mm)	I_0	0,323	0,242	0,161	0,121	A
6 Stall torque	M_H	2 642	2 760	2 887	2 911	mNm
7 Friction torque	M_R	10	10	10	10	mNm
8 Speed constant	k_n	300	225	150	112	min ⁻¹ /V
9 Back-EMF constant	k_E	3,332	4,443	6,665	8,887	mV/min ⁻¹
10 Torque constant	k_M	31,82	42,43	63,65	84,86	mNm/A
11 Current constant	k_I	0,031	0,024	0,016	0,012	A/mNm
12 Slope of n-M curve	$\Delta n / \Delta M$	2	1,9	1,8	1,8	min ⁻¹ /mNm
13 Rotor inductance	L	60	110	240	430	μ H
14 Mechanical time constant	τ_m	3,4	3,3	3,3	3,3	ms
15 Rotor inertia	J	164	164	171	171	gcm ²
16 Angular acceleration	α_{max}	161	168	169	170	$\cdot 10^3$ rad/s ²
17 Thermal resistance	R_{th1} / R_{th2}	1,9 / 4,2				K/W
18 Thermal time constant	τ_{w1} / τ_{w2}	58 / 910				s
19 Operating temperature range:						
– motor		-30 ... +125				°C
– winding, max. permissible		+155				°C
20 Shaft bearings		ball bearings, preloaded				
21 Shaft load max.:						
– with shaft diameter		6				mm
– radial at 3 000 min ⁻¹ (3 mm from bearing)		60				N
– axial at 3 000 min ⁻¹		6				N
– axial at standstill		50				N
22 Shaft play:						
– radial	\leq	0,015				mm
– axial	$=$	0				mm
23 Housing material		steel, black coated				
24 Mass		550				g
25 Direction of rotation		clockwise, viewed from the front face				
26 Speed up to	n_{max}	6 000				min ⁻¹
27 Number of pole pairs		1				
28 Magnet material		NdFeB				
Rated values for continuous operation						
29 Rated torque	M_N	139	182	222	224	mNm
30 Rated current (thermal limit)	I_N	5	5	4,3	3,2	A
31 Rated speed	n_N	5 190	5 240	5 350	5 360	min ⁻¹


Note: Rated values are calculated with nominal voltage and at a 22°C ambient temperature. The R_{th2} value has been reduced by 25%.

Note:


The diagram indicates the recommended speed in relation to the available torque at the output shaft for a given ambient temperature of 22°C.

The diagram shows the motor in a completely insulated as well as thermally coupled condition (R_{th2} 50% reduced).

The nominal voltage (U_N) curve shows the operating point at nominal voltage in the insulated and thermally coupled condition. Any points of operation above the curve at nominal voltage will require a higher operating voltage. Any points below the nominal voltage curve will require less voltage.



Dimensional drawing



Options

Example product designation: **3890H024CR-158**

Option	Type	Description
U	Single Leads	For motors with single leads (PTFE), length 160 mm, red (+) / black (-)
158	Shaft end	No second shaft end
2016	Encoder combination	Motor with rear end shaft for combination with Encoder IE3, IERS3 and IER3

Product combination

Precision Gearheads / Lead Screws	Encoders	Drive Electronics	Cables / Accessories
38A 38/1 38/1 S 38/2 38/2 S 44/1	IE3-1024 IE3-1024 L IERS3-500 IERS3-500 L IER3-10000 IER3-10000 L	SC 2804 S SC 5004 P SC 5008 S MCDC 3006 S MC 5010 S	MBZ To view our large range of accessory parts, please refer to the "Accessories" chapter.