

Motion Controllers

V2.5, 4-Quadrant PWM with RS232 or CAN interface

MCBL 3003 P AES

Values at 22°C		MCBL 3003 P AES	
Power supply electronic	U_B/U_{EL}	12 ... 30	V DC
Power supply motor ¹⁾	$-/U_B$	0 ... 30	V DC
PWM switching frequency	f_{PWM}	78,12	kHz
Efficiency electronic	η	95	%
Max. continuous output current	I_{cont}	3	A
Max. peak output current ²⁾	I_{max}	10	A
Standby current for electronic (at $U_B=24V$)	I_{el}	0,06	A
Operating temperature range		-40 ... +85	°C
Mass		18	g

¹⁾ Only available for option 3085 (separate power supply)

²⁾ S2 mode for max. 2s

Interfaces	MCBL 3003 P AES RS	MCBL 3003 P AES CF	MCBL 3003 P AES CO
Interface	RS232	CAN (FAULHABER channel)	CAN (CiA)
Protocol	FAULHABER - ASCII	CANopen	CANopen

Basic features

- Supported sensor systems:
absolute encoders AES-4096 / AESM-4096
- Positioning resolution when using absolute encoders as position encoder: 4096 steps per revolution
- Max. 3 digital inputs, max. 1 digital output, 1 analog input.
Not all I/Os available depending on wiring
- Setpoint specification via fieldbus, quadrature signal, pulse and direction or analog inputs
- Optional stand-alone operation via application programs with the RS232 interface version

Range of functions

Operating modes (RS and CF Versions)	Position, speed and torque control with setpoint specification via interface or analog. Position control with Gearing Mode or stepper motor operation. Operation as Servo Amplifier in voltage controller mode
Operating modes (CF and CO Versions)	Profile Position Mode (PP), Profile Velocity Mode (PV), Homing Mode.
Speed range for brushless motors with number of pole pairs 1	5 min ⁻¹ ... 30 000 min ⁻¹ (with sinus commutation)
Application programs	Available in versions with RS232 interface
Additional functions	Overload protection for electronics and motor, self-protection from overheating, over-voltage protection in generator mode.
Indicator	Trace as logger
Motor types	Brushless DC-motors with absolute encoders and number of pole pairs 1 or 2

