

Linear DC-Servomotors

3,6 N

with Analog Hall Sensors

LM 1247 ... 11

Values at 22°C	LM 1247 ... 11		
Continuous force	$F_{e \max.}$	3,6	N
Peak force	$F_{p \max.}$	10,5	N
Continuous current	$I_{e \max.}$	0,55	A
Peak current	$I_{p \max.}$	1,64	A
Back-EMF constant	k_E	5,25	V/m/s
Force constant	k_F	6,43	N/A
Terminal resistance, phase-phase	R	13,17	Ω
Terminal inductance, phase-phase	L	820	μH
Thermal resistance	R_{th1} / R_{th2}	3,2 / 20	K/W
Thermal time constant	τ_{w1} / τ_{w2}	11 / 624	s
Operating temperature range		-20 ... +125	°C
Magnetic pitch	τ_m	18	mm
Rod bearings		polymer sleeves	
Housing material		metal, non-magnetic	
Direction of movement		electronically reversible	

	LM 1247-	020-11	040-11	060-11	080-11	100-11	120-11	
Stroke length	$S_{\max.}$	20	40	60	80	100	120	mm
Repeatability	σ_r	40	40	40	40	40	40	μm
Accuracy	σ_a	120	140	160	180	200	220	μm
Acceleration	$a_{e \max.}$	187,6	142,5	122,9	101,8	91,4	81	m/s^2
Speed	$v_{e \max.}$	1,9	2,4	2,7	2,9	3	3,1	m/s
Rod length	$L1$	82	109	127	154	172	190	mm
Rod mass	m_m	19	25	29	35	39	44	g
Total mass	m_t	58	64	68	74	78	83	g

Note: These motors are for operation with DC-voltage < 75 V DC. The given values are for free standing motors.
Other rod lengths available on request.

Motor characteristic curves

Trapezoidal motion profile ($t_1 = t_2 = t_3$)

Displacement distance: 20 mm
Friction coefficient: 0,2
Slope angle: 0°
Rest time: 0,1 s


Load:

The max. applicable load (incl. rod) at a given speed with an external force of 0 N


External force:

The max. permissible external force at a given speed with a load (incl. rod) of:

- 0,1 kg ———
- 0,2 kg - - - - -
- 0,5 kg ⋯⋯⋯




Dimensional drawing



Option, cable and connection information

Example product designation: **LM1247-020-11**

Option	Type	Description	Connection				
			-11/-11C		-01		
			No.	Function	No.	Function	Color
-11C	Connector 	Material PVC, 10 conductors, AWG 28 with connector A05a - TCO, pitch 2 mm	1	Phase C	1	Phase C	yellow
			2	Phase B	2	Hall sensor A	green
			3	Phase A	3	U _{DD} (+5V)	red
			4	GND	4	GND	black
			5	U _{DD} (+5V)	5	Hall sensor B	blue
			6	Hall sensor C	6	Hall sensor C	grey
			7	Hall sensor B	7	Phase B	orange
			8	Hall sensor A	8	Phase A	brown
			9	N.C.	9	N.C.	white
			10	N.C.	10	N.C.	purple
			Standard cable				
			Material PVC, 10 conductors, AWG 28, grid 1mm, wires tinned.				

Product combination

Drive Electronics	Cables / Accessories
MCLM 3002 P MCLM 3002 S MCLM 3003 P MCLM 3006 S MC 3001 B MC 3001 P MC 5004 P MC 5004 P STO MC 5005 S	To view our large range of accessory parts, please refer to the "Accessories" chapter.